


BAL SEAL® SEALS IN TATTOOING PIGMENT APPLICATORS

An applicator design must be light and fit easily into the user's hand. The basic operation of a rotating cam transfers motion to a wobble plate, which moves a reciprocating needle.

At the applicator tip, two Bal Seals are placed to protect and retain the fluid in the drive mechanism and to keep the pigment fluids from leaking. These components must operate freely and contribute minimally to power loss.



Operating Parameters

Pressure:	Atmospheric to autoclaved 30 psi (2 kg/cm ²)
Temperature:	70°F to autoclaved 275°F (21°C to 135°C)
Media:	Pigment, bearing grease and sterilization fluids
Additional:	Low friction and autoclavable

Seal Selection: PB

Features:

- Low friction to keep responsive needle motion.
- Bearing grease kept from weeping into the environment, and environmental contaminants kept out.
- Pigment sealed from electro-drive mechanism.
- Bal Seal seals withstand autoclave temperatures.
- Excellent sealing performance through autoclave sterilization.
- Filled PTFE seal materials operate unlubricated and are FDA-compatible.*

For more information and technical assistance, consult the Technical Sales Department.

PATENTS: The items described in this page include products that are the subject of issued United States and foreign patents or products where patents are pending, including the following: Patents 6,641,141 B2; 7,210,398 B2; 6,161,838; 5,992,856; 5,134,244
U.S. Address 19650 Pauling Foothill Ranch, CA 92610-2610 • Phone: (949) 460-2100 • Fax: (949) 460-2300

BV Address: Jollemanhof 16, • 1019 GW Amsterdam • The Netherlands • Phone: 31 20 638 65 23 • Fax: 31 20 625 60 18

Bal Seal Engineering, Inc. is certified to ISO 9001 | www.balseal.com