


BAL SEAL® SPRING-ENERGIZED SEALS IN GAS-OPERATED PISTON DISPENSING PUMPS

Gas-operated piston dispensing pumps control the delivery of liquids for a variety of medical, chemical, and laboratory applications. Pressurized nitrogen gas forces the reciprocating piston downward, and then the piston is spring-returned.

Retracting the piston creates a vacuum intake of a precise volume of liquid. Extending the plunger produces a low-pressure liquid discharge. Bal Seal[®] spring-energized seals in ball-check valves control the flow.



Seal Selection: Liquid Plunger Seal

The 64X cover Bal Seal spring-energized seal shown in View A is recommended for gas-operated piston dispensing pumps, which require a high degree of chemical compatibility and low dead volume.

Pumped media does not come in contact with the energizing spring. The 64X seal has a snap-on locking feature for ease of assembly and permanently locks the seal onto the piston.

Gas Piston Seal

The KCX piston seal shown in View B is retained onto the piston by the metal locking ring. The KCX is designed to provide low friction, while offering excellent sealing reliability. The unique, patented, Bal Spring® canted coil spring energizer provides a near-constant force for long seal life.

At both low and high deflections, the seal compensates for wear and dimensional variations while maintaining a generally constant force.

For more information and technical assistance, contact a technical sales representative.

PATENTS: The items described in this page include products that are the subject of issued United States and foreign patents or products where patents are pending, including the following: Patents 6,641,141 B2; 7,210,398 B2; 6,161,838; 5,992,856; 5,134,244

e patents are pending, including the following: Patents 6,641,141 B2; 7,210,398 B2; 6,161,838; 5,992,856; 5,134,244

U.S. Address: 19650 Pauling Foothill Ranch, CA 92610-2610 • Phone: (949) 460-2100• Fax: (949) 460-2300

BV Address: VIDA Building, First Floor • Kabelweg 57 • 1014 BA Amsterdam • The Netherlands • Phone: 31 20 638 65 23 • Fax: 31 20 625 60 18

Bal Seal Engineering is certified to ISO 9001 | www.balseal.com